

[See all 24 Products in Family](#)

Ti:Sapphire Flat Top Beam Shaper 12mm | πShaper 12_12_TiS_HP

See More by [AdlOptica](#)



Stock **#14-279** [CONTACT US](#)

-

1

+

S\$14,062⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$14,062.00 each
Qty 5-10	S\$12,663.00 each
Qty 11+	S\$11,958.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:

πShaper 12_12_TiS_HP

Type:

Beam Shaper

Style:

Flat Top

Physical & Mechanical Properties

358.00	Length (mm):
<530	Weight (g):

42.00	Diameter (mm):
-------	----------------

Optical Properties

12.0 - 12.1	Entrance Beam Diameter, 1/e ² (mm):
800	Design Wavelength DWL (nm):

700 - 900	Wavelength Range (nm):
3000 mJ/cm ² @ 5ns (typical)	Damage Threshold, By Design: ☐

12.0	Output Diameter, FWHM (mm):
3000 mJ/cm ² @ 5ns (typical)	Damage Threshold, Pulsed:

Threading & Mounting

M27 x1	Mounting Threads:
--------	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica πShaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, and system integration. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica πShaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO2 laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

Note: Focusing a flat-top beam after a πShaper results in loss of the flat top profile. [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information

