

Coherent® USB PowerMax Pro Measurement System 1295921 | 150W

See More by [Coherent®](#)



Coherent USB-PowerMax Pro Fast Measurement Systems

Stock **#37-075** **2 In Stock**

S\$5,467⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$5,467.00 each
Need More?	Request Quote

Product Downloads

General

1295921 **Model Number:**

Meterless **Type:**

≤10 **Rise Time (µs):**

±2 **Calibration Uncertainty (%):**

Cooling Method:

Water/Air (intermittent)

≤10 **Fall Time (μs):**

Maximum Incident Energy Density:
33mJ/cm² (10ns; 1064nm)

Physical & Mechanical Properties

30 x 30 **Active Area (mm):**

Optical Properties

810 **Calibration Wavelength (nm):**

400 - 1100, 9000 - 11000 **Wavelength Range (nm):**

Electrical

±3 **Spectral Compensation Accuracy (%):**

14 **Maximum Incident Power Density (kW/cm²):**

200mW to 150W **Power Range (Water-Cooled):**

Hardware & Interface Connectivity

2.5 **Length of Cable (m):**

USB **Computer Interface:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- Fastest Response Laser Power Measurement System Available
- Fully Integrated Plug-and-Play USB System
- Large Active Area for Full Beam Measurement

Coherent USB-PowerMax Pro Fast Measurement Systems incorporate a patented power sensor technology that delivers orders of magnitude faster response time than previously possible with thermal or pyro detector technology. The systems enable users to measure laser average power, peak power, and pulse energy, while viewing the pulse temporal profile of the beam. They are ideal for process control due to the instantaneous response to laser power variation and detailed pulse analysis, without impacting process throughput. Coherent USB-PowerMax Pro Fast Measurement Systems eliminate the need for a separate meter and feature a small form factor, simple implementation, and easy communication via direct USB interface, or wirelessly through available Android™ and iOS applications.