

TECHSPEC[®] 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens



1.7X Magnification, #63-232

Stock **#63-232** 20+ In Stock

-

1

+

S\$3,007⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$3,007.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

PlatinumTL™ Series

Series:

[#63-233](#) Sold Separately

Stock No. of Mounting Clamp:

Telecentric Lens

Type:


Physical & Mechanical Properties	
Variable	Iris Option:
189.50	Length (mm):
60.0	Maximum Diameter (mm):
746	Weight (g):
17.5	Flange Distance (mm):
Optical Properties	
5.2mm	Horizontal Field of View, 2/3" Sensor:
3.7mm	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
0.083	Numerical Aperture NA, Object Side:
10 (7)	Number of Elements (Groups):
<0.080	Typical Telecentricity @ 588nm (°):
<0.020	Typical Distortion @ 588nm (%):
1.7X	Primary Magnification PMAG:
1.70	Telecentric Lens Magnification:
123.00	Working Distance (mm):
5.2 x 3.9	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±0.18 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
1.7X	Magnification:
VIS	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):
Threading & Mounting	
M58 x 0.75 (Female)	Filter Thread:
C-Mbunt	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mbunt, T-Mount, F-Mbunt Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.


TECHNICAL INFORMATION




#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Distortion Plot




#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Relative Illumination Plot




#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Telecentricity Plot



#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 123mm Working Distance, f6



#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 123mm Working Distance, f6



#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 123mm Working Distance, f10



#63-232, 1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 123mm Working Distance, f10

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mbunt	#62-933	17.5mm	230.8mm	60.5mm	33.5mm
0.5X	C-Mbunt	#62-932	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mbunt	#63-232	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mount	#62-922	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	#62-923	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	#62-924	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mount	#62-912	46.5mm	143mm	90mm	55mm
	M42 x 1.0	#62-913	6.56mm	184mm	90mm	50mm
	M42 x 1.0	#62-914	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mbunt	#62-902	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	#62-903	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	#62-904	19.53mm	197.8mm	65mm	53mm

