


1" x 1", Line Grid Low Reflective Chrome



Line Grid Low Reflective Chrome

Stock #62-537 CLEARANCE 12 In Stock

⊖ 1 ⊕ \$917⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$917.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

25.40 Length (mm):

±0.002 Overall Accuracy (mm):

20.0 x 20.0 Pattern Size (mm):

2.50 Thickness (mm):

25.40 Width (mm):

Line Thickness (mm):
Center Line: 0.125 ±0.005
Inner Line: 0.075 ±0.005

Center to Center Spacing (mm):
1.00 ±0.001

Optical Properties

Substrate: □
White Soda Lime Glass

Optical Density OD (Average):
>3.0

Surface Quality:
20-10 over active area, 60-40 outside

Surface Flatness (P-V):
3 - 4λ

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Product Details

- Test and Correction of Distortion in Vision Systems
- Calibration of Perspective Error in Microscope Stages
- Measure Physical Field of View

Line Grid Targets are designed for calibrating vision systems and microscope stages via repeated parallel lines in both X and Y axes. Using these lines as a reference, distortion and perspective error can be quantified and calibrated out of a system. Line Grid Targets are available as Chrome on Clear Float Glass, and Low Reflection Chrome on White Soda Lime Glass. The Chrome on Clear Float Glass is transparent and can be used for transmissive illumination via back lighting, while the Low Reflection Chrome on White Soda Lime Glass can be used for reflective illumination with front lighting, without creating highlights that degrade the image of the target.