

[See all 33 Products in Family](#)

20 x 20mm, 800µm Pitch, 1.7° Div., Double Cyl. Lens Array UV-VIS



Stock #72-606 **3 In Stock**

S\$1,311⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$1,311.00 each
Qty 11-25	S\$1,053.00 each
Qty 26-49	S\$983.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array Type:

Physical & Mechanical Properties

20.0 x 20.0 ±0.10 Dimensions (mm):

11.100 Radius R (mm):

2.00 ±0.10 **Thickness (mm):**

Optical Properties

Effective Focal Length EFL (mm):
24.70 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
UV-NIR (250-700nm)

Wavelength Range (nm):
250 - 700

Coating Specification:
R_{abs} ≤1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤1.5% @ 250 - 700nm @ 0°

Divergence Angle (°):
1.7 (Full Width)

Pitch (µm):
800.00

Array Type:
Double-Sided (with cross-oriented lenses)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.