

TECHSPEC<sup>®</sup> 20mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-416** 9 In Stock

-

1

+

S\$298<sup>79</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$298.70 each                |
| Qty 6+         | S\$268.83 each                |
| Need More?     | <a href="#">Request Quote</a> |

| Product Downloads |
|-------------------|
|-------------------|

SPECIFICATIONS

General

Laser Mirror

Type:

Physical & Mechanical Properties

Diameter (mm):

|                                                                                                                     |                             |
|---------------------------------------------------------------------------------------------------------------------|-----------------------------|
| 20.00 +0.00/-0.20                                                                                                   |                             |
| >90                                                                                                                 | Clear Aperture (%):         |
| 30                                                                                                                  | Parallelism (arcsec):       |
| 3.00 +/-0.2                                                                                                         | Thickness (mm):             |
| Optical Properties                                                                                                  |                             |
| 355                                                                                                                 | Design Wavelength DWL (nm): |
| 351 - 358                                                                                                           | Wavelength Range (nm):      |
| ZERODUR®                                                                                                            | Substrate: <div></div>      |
| 45                                                                                                                  | Angle of Incidence (°):     |
| 99.8                                                                                                                | Reflection at DWL (%):      |
| Laser Mirror (355nm)                                                                                                | Coating:                    |
| Coating Specification:<br>R <sub>abs</sub> >99.8% @ 355nm @ 45° AOI R <sub>avg</sub> >99.5% @ 351 - 358nm @ 45° AOI |                             |
| Dielectric                                                                                                          | Coating Type:               |
| λ/10                                                                                                                | Surface Flatness (P-V):     |
| 20-10                                                                                                               | Surface Quality:            |
| Damage Threshold, By Design: <div></div><br>6 J/cm² @ 355nm, 20ns, 20Hz                                             |                             |
| Regulatory Compliance                                                                                               |                             |
| View                                                                                                                | Certificate of Conformance: |

## PRODUCT DETAILS

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems