

[See all 5 Products in Family](#)

## 20mm Dia. x 20mm EFL Arton Plastic Asphere, Coated



Stock #90-325 **14 In Stock**

S\$95<sup>.20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	S\$95.20 each
Qty 11-49	S\$79.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Aspheric Lens Type:

#### Physical & Mechanical Properties

20.00 Diameter (mm):

16.00 Clear Aperture CA (mm):

4.8 Edge Thickness ET (mm):

Protective as needed **Bevel:**

17.28 **Flange Distance (mm):**

### Optical Properties

20.00 ±0.2 **Effective Focal Length EFL (mm):**

0.40 **Numerical Aperture NA:**

17.28 **Back Focal Length BFL (mm):**

Arton Plastic **Substrate:** □

BBAR (650-850nm) **Coating:**

R<sub>abs</sub> <1.0% @ 650 - 850nm **Coating Specification:**

1.25 **f#:**

57.0 **Abbe Number (v<sub>d</sub>):**

650 - 850 **Wavelength Range (nm):**

Infinite **Conjugate Distance:**

### Regulatory Compliance


[View](#) **Certificate of Conformance:**

## Product Details

- Superior Durability for Harsh Environments
- High Heat Resistance
- Low Water Absorbency

Arton® Plastic Aspheric Lenses are ideal alternatives to PMMA or polycarbonate plastic aspheric lenses for weight sensitive, harsh environment applications. Typical plastic substrates degrade in performance in hot or humid environments. Arton®, a polyolefin thermoplastic plastic substrate, maintains plastic's high translucency and low birefringence, while featuring increased heat resistance and decreased water absorbency.

## Technical Information



## Compatible Mounts