

[See all 11 Products in Family](#)

# 20mW 320nm OBIS XT

See More by [Coherent®](#)



Stock #75-316 NEW CONTACT US

⊖ 1 ⊕ S\$41,944<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	S\$41,944.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Warm-Up Time (minutes):**  
<5

**Manufacturer:**  
Coherent®

**Type of Laser:**  
Diode Pumped Solid State

**Laser Class - CDRH:**  
IIIb

**Model Number:**  
1371110

**Physical & Mechanical Properties**

125.0 x 70.0 x 36.5	<b>Dimensions (mm):</b>
450	<b>Weight (g):</b>
<5	<b>Pointing Stability (µrad/°C):</b>
<30	<b>Pointing Stability (µrad):</b>
<b>Optical Properties</b>	
100:1	<b>Polarization:</b>
TEM <sub>00</sub>	<b>Spatial Mode:</b>
319.80	<b>Wavelength (nm):</b>
≤1.1	<b>Mode Quality, M<sup>2</sup>:</b>
±0.05	<b>Beam Diameter Tolerance (mm):</b>
0.7	<b>Beam Diameter (mm):</b>
Full-Angle: <0.7	<b>Beam Divergence (mrad):</b>
UV	<b>Color:</b>
<b>Electrical</b>	
20	<b>Output Power (mW):</b>
≤0.25% (20Hz to 20MHz)	<b>RMS Noise:</b>
<b>Hardware &amp; Interface Connectivity</b>	
Free Space	<b>Output Type:</b>
<b>Environmental &amp; Durability Factors</b>	
+10 to +35	<b>Operating Temperature (°C):</b>
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Compact, Thermally Efficient Design for Ease of Life Science System Integration
- 320, 349, and 640nm Wavelength Options Available
- Integrated Controller with RS-232, RS-485, and USB Interfaces

Coherent OBIS XT Laser Systems offer an advanced extension of the [OBIS LS/LX](#), delivering powerful performance across ultraviolet and visible wavelengths. These lasers are available in UV wavelengths of 320 and 349nm, with output power options ranging from 20 to 150mW, and a higher-power 640nm wavelength option with output powers of 400 or 500mW. Flexible communication interfaces, including RS-232, RS-485, and USB, allow for seamless integration and real-time control in complex applications. Coherent OBIS XT Laser Systems are designed to simplify system integration, utilizing their compact form factor, integrated controller, as well as a low thermal output. This reduces the need for external cooling and streamlines OEM and end-user implementation. OBIS XT lasers are ideal for a wide range of applications, including life sciences, biomedical, flow cytometry, DNA Sequencing, and fluorescence microscopy.