


## 21mm Dia., Metric Concentric Square, Contact Reticule



Metric Concentric Squares

Stock #64-850 CLEARANCE **4 In Stock**

S\$54<sup>MS</sup>

ADD TO CART

### Volume Pricing

Qty 1+	S\$54.95 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric Concentric Squares **Type:**

### Physical & Mechanical Properties

21.00 ±0.05 **Diameter (mm):**

2.28 ±0.127 **Thickness (mm):**

±2 **Line to Line Accuracy (µm):**

<30	Parallelism (arcsec):
0.25	Centering (mm):
25.00	Line Thickness (µm):
±13	Line Thickness Tolerance (µm):

## Optical Properties

±1	Angle Tolerance (arcsec):
60-40	Surface Quality:
Glass	Substrate: <input type="checkbox"/>
3 - 4λ	Surface Flatness (P-V):

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 209:
<a href="#">View</a>	Certificate of Conformance:

## Product Details

- Greater Stability than Film Reticles
- Low Reflection Chrome Pattern
- Protractor, Crosshair, or Concentric Square Patterns

Circular Scale Contact Reticles offer greater stability than film reticles which can bend, warp, and can easily be damaged. The patterns on these reticles are low reflection chrome deposition for high contrast and easy readability. Markings are on the outside of the reticle, so the scales are always in direct contact with the object under view. This provides optimum focus and accurate measurements. Circular Scale Contact Reticles, in the 21mm and 27mm size, are for use with our [6X and 9X comparators](#) and our 26mm and 35mm diameter reticles are for use with our [Peak Measuring Loupes](#) and our [Peak Illuminated Magnifiers](#). Please note the field of view specified for the magnifiers before selecting a magnifier/reticle combination. For example, the 5/8" (16mm) field of view for a 12X comparator may not be suitable for use with a reticle that has a 3/4" (20mm) scale if the full scale is needed.