

[See all 18 Products in Family](#)

## 25.4mm Dia. 366nm $\lambda/2$ Quartz Waveplate



Stock #71-401 [CONTACT US](#)

⊖ 1 ⊕ **\$777<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-5	<b>\$777.00</b> each
Qty 6+	<b>\$540.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Crystalline Waveplate **Type:**

### Physical & Mechanical Properties

>20.00 **Clear Aperture CA (mm):**

25.40 +0.0/-0.2 **Diameter (mm):**

### Optical Properties

366	<b>Design Wavelength DWL (nm):</b>
Crystalline Quartz	<b>Substrate:</b> <input type="checkbox"/>
$\lambda/2$	<b>Retardance:</b>
20-10	<b>Surface Quality:</b>
$\lambda/180 @ 20C$	<b>Retardance Tolerance:</b>
$\lambda/10 @ 632.8nm$	<b>Transmitted Wavefront Distortion (RMS):</b>
R<0.3% @ 366nm on each surface	<b>Coating Specification:</b>
Zero	<b>Retardance Order:</b>
Anti-Reflection	<b>Coating Type:</b>

## Threading & Mounting

6.00 ±0.2	<b>Mount Thickness (mm):</b>
Anodized Aluminium	<b>Mount:</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Ideal for Trapped-Ion and Neutral Atom Applications
- Range of Application-Specific Wavelengths from UV to NIR
- 12.7 and 25.4mm Diameters for Easy Integration

Half Waveplates for Quantum Computing are ideal for the manipulation of polarization states in trapped ion, linear optical, and neutral atom quantum computing, as well as quantum cryptography and communication applications. These waveplates are available in a range of commonly-used, application-specific wavelengths across the UV to NIR spectrum covering the main wavelengths of commonly used ions (Ytterbium/Strontium/Calcium), and offer a retardance of  $\lambda/2$  and a retardance accuracy of  $\lambda/200$ .

Depending on wavelength, these waveplates feature either a first or zero-order construction for a low temperature-sensitivity, and are AR-coated for maximum transmission at the design wavelength to ensure optimal performance with low light signals. Half Waveplates for Quantum Computing are housed in a black, anodized aluminum mount and are available in both a 1" and more compact  $\frac{1}{2}$ " size for easy integration into space sensitive systems. Polarizing Cube Beamsplitters for Quantum Computing are also available, and custom wavelengths are available for both.

## Technical Information

Wavelength (nm)	Application Type
366	Trapped Ion
392	Trapped Ion
435	Trapped Ion
495	Trapped Ion
679	Neutral Atom
689	Neutral Atom
795	Neutral Atom
813	Neutral Atom
815	Neutral Atom