

[See all 44 Products in Family](#)

**TECHSPEC® 25.4mm Dia., 532 & 1064nm T, 266nm R 0° Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock #22-659 **15 In Stock**

⊖ 1 ⊕ **\$533<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>\$533.40</b> each
Qty 6-24	<b>\$480.20</b> each
Qty 25-49	<b>\$427.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Harmonic Beamsplitter **Type:**

**Physical & Mechanical Properties**

>90 **Clear Aperture (%):**

Dichroic **Construction:**

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

6.35 ±0.20 **Thickness (mm):**

## Optical Properties

0 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >95% @ 266nm, T<sub>abs</sub>: >98% @ 532nm, T<sub>abs</sub>: >98% @ 1064nm  
Surface 2: R<sub>abs</sub>: <1.0% @ 532nm, R<sub>abs</sub>: <1.0% @ 1064nm

266 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532, 1064 **Transmission Wavelength (nm):**

**Damage Threshold, By Design:**   
Surface 1: 1 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz  
5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
7.5 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz  
Surface 2: 10 J/cm<sup>2</sup> @ 20ns, 20Hz @ 532nm  
15 J/cm<sup>2</sup> @ 20ns, 20Hz @ 1064nm

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

## Compatible Mounts