

[See all 44 Products in Family](#)

TECHSPEC® 25.4mm Dia., 532 & 1064nm T, 266nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock **#11-546** [CONTACT US](#)

⊖ 1 ⊕ **\$\$533⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$\$533.40 each
Qty 6-24	\$\$480.20 each
Qty 25-49	\$\$427.00 each
Need More?	Request Quote

Product Downloads

General

Harmonic Beamsplitter **Type:**

Physical & Mechanical Properties

>90 **Clear Aperture (%):**

Dichroic **Construction:**

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

6.35 ±0.20 **Thickness (mm):**

Optical Properties

45 **Angle of Incidence (°):**

Coating Specification:
Surface 1: $R_{\text{abs}} > 95\%$ @ 266nm, $T_{\text{abs}} > 98\%$ @ 532nm, $T_{\text{abs}} > 98\%$ @ 1064nm
Surface 2: $R_{\text{abs}} < 1.0\%$ @ 532nm, $R_{\text{abs}} < 1.0\%$ @ 1064nm

266 **Reflection Wavelength (nm):**

Substrate:
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532, 1064 **Transmission Wavelength (nm):**

Damage Threshold, By Design:
Surface 1:
1 J/cm² @ 266nm, 20ns, 20Hz
5 J/cm² @ 532nm, 20ns, 20Hz
7.5 J/cm² @ 1064nm, 20ns, 20Hz
Surface 2:
10 J/cm² @ 20ns, 20Hz @ 532nm
15 J/cm² @ 20ns, 20Hz @ 1064nm

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

Compatible Mounts