

[See all 12 Products in Family](#)

25.4mm Dia. Left-Handed VIS-Coated Glass Circular Polarizer (CP42HE)



Stock #19-936 **20+ In Stock**

⊖ 1 ⊕ \$96⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	\$96.60 each
Qty 10-25	\$87.36 each
Need More?	Request Quote

Product Downloads

General

Left-Handed Circular Polarizer **Type:**

Physical & Mechanical Properties

25.40 **Diameter (mm):**

2.00 ±0.10 **Thickness (mm):**

±0.20 **Dimensional Tolerance (mm):**

Laminated Glass Polarizing Film

Construction:

Optical Properties

VS AR Coated

Coating:

Substrate:
Polymer Film CP42HE Laminated Between Glass

45 ±2

Transmission (%):

R_{avg} <0.5% @ 425 - 700nm

Coating Specification:

425 - 700

Wavelength Range (nm):

>99.90

Polarization Efficiency (%):

Environmental & Durability Factors

-40 to +80

Operating Temperature (°C):

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Uncoated and Visible AR Coated Options
- Left-Hand Circular Polarization
- Increased Durability in Machine Vision Applications

Glass Circular Polarizers (CP42HE) are designed for reducing surface reflection and glare, making them ideal for a variety of imaging applications. These circular polarizers feature a linear sheet polarizer and quarter-wave retarder laminated between two optical-grade glass windows. The window substrates provide increased rigidity and durability in industrial applications. An anti-reflection (AR) coating option provides increased transmission of visible light from 425 – 700nm. Glass Circular Polarizers (CP42HE) provide a left-handed polarization direction. Example imaging applications include machine vision, digital image processing, and photography.

Technical Information

