

TECHSPEC[®]

25.4mm Dia. x 25.4mm EFL, UV Enhanced Aluminum 90° OAP Mirror with Alignment Through Holes



#11-768

Stock **#11-768** 1 In Stock

-

1

+

S\$413⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$413.00 each
Qty 6-10	S\$372.40 each
Qty 11-25	S\$351.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Off-Axis Parabolic Mirror

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.00/-0.10

<50 RMS	Surface Roughness (□):
25.40	Y Offset (mm):
Through Hole Orientation: 1 x Parallel to Focused Beam 1 x Parallel to Collimated Beam	

4.1	Through Hole Diameter (mm):
-----	-----------------------------

Optical Properties

25.40	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):

25.40	Radius of Curvature (mm):
Enhanced Aluminum (250-700nm)	Coating:

Metal	Coating Type:
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:

90	Off-Set Angle (°):
12.7	Parent Focal Length PFL (mm):

λ/8	Surface Figure, RMS:
250 - 700	Wavelength Range (nm):

80-50	Surface Quality:
Aluminum 6061-T6	Substrate:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------


Product Details

- Through Holes Parallel to Focused and Collimated Beams
- Range of Metallic Coatings Available
- <50ÅRMS Surface Roughness

TECHSPEC® Off-Axis Parabolic (OAP) Mirrors with Alignment Through Holes are designed with two through holes, one that aligns with the focal point of beams focused off the parabolic surface and the second parallel to beams collimated by the surface. The hole placements allow for two beams to hit a target or sample simultaneously, which is a technique used to take pump-probe measurements. These OAPs feature aluminum substrates and are diamond turned with a surface roughness of <50ÅRMS that minimizes scatter. TECHSPEC Off-Axis Parabolic Mirrors with Alignment Through Holes are available coated with protected gold, protected aluminum, or UV enhanced aluminum for integration into applications requiring high reflectance from the ultraviolet (UV) to the infrared (IR).

Note: Please [contact us](#) for custom options if your application requires a [standard OAP Mirror](#) with a through hole.

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).