


[See all 3 Products in Family](#)

**TECHSPEC® 25.4mm Enhanced Aluminum Coated  $\lambda/10$  Knife-Edge Pickoff Mirror**



25.4mm Enhanced Aluminum Coated  $\lambda/10$  D-Shaped Pickoff Mirror, #36-135

Stock **#36-135** [CONTACT US](#)

⊖ 1 ⊕ **S\$125<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$125.30</b> each
Qty 6-25	<b>S\$113.40</b> each
Qty 26+	<b>S\$100.10</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

25.40 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

Fine Grind	<b>Back Surface:</b>
Protective as needed	<b>Bevel:</b>
<hr/>	
+0.0/-0.20	<b>Dimensional Tolerance (mm):</b>
Ground	<b>Edges:</b>
<hr/>	
2	<b>Parallelism (arcmin):</b>

## Optical Properties

Metal	<b>Coating Type:</b>
Enhanced Aluminum (450-650nm)	<b>Coating:</b>
<hr/>	
$\lambda/10$	<b>Surface Flatness (P-V):</b>
450 - 650	<b>Wavelength Range (nm):</b>
<hr/>	
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
$R_{avg} > 95\%$ @ 450 - 650nm	<b>Coating Specification:</b>
<hr/>	
20-10	<b>Surface Quality:</b>
<hr/>	
0.2 J/cm <sup>2</sup> @ 532nm, 10ns	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

## Regulatory Compliance


<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<hr/>	
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Designed to Separate Two Beams Propagating Closely Next to Each Other
- 45° Bevel
- Coating Aperture Up to the Knife-Edge
- Enhanced Aluminum, Protected Gold and Protected Silver Coating Options

Knife-Edge Pickoff Mirrors are designed to selectively reflect an individual beam from a group of tightly spaced beams, while minimizing the overall footprint of the application. These mirrors feature a sharp 45° bevel with a reflective coating that extends to the beveled edge on a precision Fused Silica substrate with  $\lambda/10$  flatness to the bevel. Knife-Edge Pickoff Mirrors are ideal for applications that incorporate dispersion prisms and diffraction gratings. These mirrors are available in three metallic coating options with performance from the visible spectrum into the far IR.

## Technical Information



## Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---

;