

[See all 14 Products in Family](#)

## 25mm Dia., 325nm Laser Line Longpass Filter



Laser Line Longpass Filters

Stock **#47-498** **1 In Stock**

⊖ 1 ⊕ **SS\$1,162<sup>56</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>SS\$1,162.56</b> each      |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

Longpass Filter **Type:**  
**Angle Tuning Range, for 0 - 8° Shift:**  
 -0.3% of Laser Wavelength

#### Physical & Mechanical Properties

25.00 +0.0/-0.1 **Diameter (mm):**  
 22 **Clear Aperture CA (mm):**

88

Clear Aperture (%):

### Optical Properties

0 ±2 **Angle of Incidence (°):**

>400 **Bandwidth (nm):**

200 - 325 **OD 6 Blocking Wavelength Range (nm):**

≥6.0 **Optical Density OD (Average):**

325 **Design Wavelength DWL (nm):**

**Substrate:**   
[Fused Silica](#) (Coming 7980)

Hard Coated **Coating:**

60-40 **Surface Quality:**

90.00 **Transmission (%):**

329.2 - 733.1 **Transmission Wavelength (nm):**

1.60 **Edge Steepness (nm):**

<3.3 **Transition Width (nm):**

325 **Laser Blocking Wavelength (nm):**

**Damage Threshold, By Design:**   
0.5 J/cm<sup>2</sup> @ 266nm, 10ns, 10Hz  
1 J/cm<sup>2</sup> @ 532nm, 10ns, 10Hz

### Threading & Mounting

3.5 **Mount Thickness (mm):**

### Environmental & Durability Factors

**Durability:**  
Environmental: ML-STD-810F, Physical: ML-C-48497A

<5 **Temperature Dependence (ppm/°C):**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 209:**

[View](#) **Certificate of Conformance:**

## Product Details

- Up to 93% Transmission to Detect Weak Signals
- Deep > OD 6 Blocking for Maximum Laser Rejection
- Ideal for Raman Spectroscopy, Confocal Microscopy, and Biotech Instrumentation
- Unrivaled Performance and Lifetime

Our Laser Line Longpass filters offer unprecedented performance in longpass laser edge filter applications. The steep edges (measured from an optical density of 6.0 to a transmission of 50%) make it possible to measure even the smallest Raman shifts, making these filters a superior alternative to costly holographic notch filters for Stokes Raman scattering measurements. Compared to notch filters, these edge filters offer better transmission, higher laser line blocking, and steeper edges, permitting measurement of Raman signals extremely close to the laser line. The large bandwidths and exceptional transmission permit these filters to be used in even the most demanding imaging applications.

## Technical Information



## Compatible Mounts

---