

TECHSPEC® 25mm Thick Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock #38-758 **9 In Stock**

⊖ 1 ⊕ S\$57⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$57.40 each
Qty 5+	S\$54.60 each
Need More?	Request Quote

Product Downloads

General

Fixed **Type:**

Optic Mount (Fixed) **Function:**

Physical & Mechanical Properties

23 **Total Length (mm):**

Min. Thickness of Compatible Optics (mm):

1.0

Max. Thickness of Compatible Optics (mm):
17.0

Clear Aperture CA (mm):
22.0

Construction:
Matte Black Anodized Aluminum (6061-T6)

Edge Thickness of Compatible Optics (mm):
17.0

Threading & Mounting

Thread Type:
M29 x 0.75

Diameter of Compatible Optics (mm):
25.0

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
- One Retainer Ring and One Delrin Ring are Included
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

Note: Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.