



[See all 29 Products in Family](#)

## 25mm Travel, Metric Micrometer, Thru-Hole Ball Bearing Stage



5" Center drive stage



Stock #33-489 **CLEARANCE** 1 In Stock

⊖ 1 ⊕ S\$1,050.<sup>00</sup>

**ADD TO CART**

|                |                               |
|----------------|-------------------------------|
| Volume Pricing |                               |
| Qty 1+         | S\$1,050.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

English **Type:**  
Thru-Hole **Note:**

### Physical & Mechanical Properties

Linear (X) **Type of Movement:**

|                        |  |
|------------------------|--|
| Ball Bearing           | <b>Guide System:</b>                         |
| Center Drive           | <b>Drive Orientation:</b>                    |
| 127 x 127              | <b>Stage Size (mm):</b>                      |
| 25                     | <b>Travel (mm):</b>                          |
| Aluminium Stage        | <b>Construction:</b>                         |
| 0.01                   | <b>Graduation (mm):</b>                      |
| 1.00                   | <b>Height (inches):</b>                      |
| 25.4                   | <b>Height (mm):</b>                          |
| 105                    | <b>Load Capacity, Normal (lbs):</b>          |
| 5.00 x 5.00            | <b>Stage Size (inches):</b>                  |
| 0.00008/inch of travel | <b>Straight Line Accuracy (inches):</b>      |
| 2.7                    | <b>Weight (lbs):</b>                         |
| 30                     | <b>Thrust Capacity, T<sub>a</sub> (lbs):</b> |
| 2.5                    | <b>Thrust Capacity, T<sub>b</sub> (lbs):</b> |

## Hardware & Interface Connectivity

|                   |                       |
|-------------------|-----------------------|
| Metric Micrometer | <b>Type of Drive:</b> |
|-------------------|-----------------------|

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |

## Product Details

[Adapter Plates](#) and [Z-Axis Brackets](#) are available for ball bearing stages and slides.

- Preloaded Ball Bearing Design for Low-Friction Linear Adjustment
- Solid-Top and Thru-Hole Versions
- English or Metric Micrometer Drive and Fine Screw Drive Available
- Stackable for 2-Axis or 3-Axis Movement

English Ball Bearing Translation Stages with an English hole pattern on both the top and bottom plates have a preloaded ball bearing design that offers straight line accuracy of 0.00008inch per inch of travel. These stages are available in a variety of stage sizes with multiple options of drive orientation, travel distance, and drive mechanism, as well as top plates with or without a clearance thru-hole. The English and Metric micrometer models offer graduations of 0.001inch or 0.01mm for applications that require a position readout while the Fine Screw (64 Pitch) models offer fine resolution positioning. English Ball Bearing Translation Stages are designed to have low friction, providing smooth linear motion without backlash or sideplay. All stages include screws for creating an X-Y stage and a position lock.

**Note:** [Adapter Plates](#) and [Z-Axis Brackets](#) are available for breadboard mounting application and X-Y-Z configuration. Brackets include screws for assembling X-Y-Z stages from multiple stages.