


25mm x 25mm, 1.1mm Thick, <math><10 \Omega/\text{sq}</math>, ITO Coated Glass Windows



Indium Tin Oxide (ITO) Coated Conductive Windows

Stock #74-465 **NEW** 20+ In Stock

S\$77⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$77.00 each
Qty 11-25	S\$61.60 each
Qty 26-49	S\$57.75 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Protective Window **Type:**

Physical & Mechanical Properties

25 x25 ±0.2	Dimensions (mm):
1.10 ±0.25	Thickness (mm):
Cut and Safety Seam	Edges:
ITO Window	Construction:
Optical Properties	
S1: ITO Coating S2: Uncoated	Coating:
<10 Ω/sq	Coating Specification:
Float Glass	Substrate: <input type="checkbox"/>
400 - 700	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Electro Magnetic Interference (EMI) Shielding, Defogging, and Display Protection Applications
- 10Ω/sq and 100Ω/sq Coating Options
- 12.5, 25, 50, and 75 mm Sizes Available
- Conductive Tape Available for Prototyping

Indium Tin Oxide (ITO) Coated Conductive Windows feature an electrically conductive coating on float glass substrates and are available in sheet resistivities of 10 Ω/sq and 100 Ω/sq. A low sheet resistivity of 10 Ω/sq is ideal for applications requiring high conductivity, while the 100 Ω/sq resistivity is commonly used for improved heat dissipation and NIR transmission. Available in both round and square sizes from 12.5 to 75 mm, the windows feature up to 88% visible light transmission in the 400-700nm range. Indium Tin Oxide (ITO) Coated Conductive Windows are ideal for a wide variety of applications including display protection, EMI shielding, outdoor surveillance, de-fogging, and de-icing applications. Additionally, conductive tape is available to simplify prototyping and integration.