

TECHSPEC<sup>®</sup> 2mm, Aluminum Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#32-526** 20+ In Stock

-

1

+

S\$147<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$147.00 each                |
| Qty 6-25       | S\$132.30 each                |
| Qty 26-49      | S\$109.90 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                             |
|----------------------------------|-----------------------------|
| Right Angle Prism                | Type:                       |
| Physical & Mechanical Properties |                             |
| ±0.1                             | Dimensional Tolerance (mm): |
| Protective as needed             | Bevel:                      |


|                                                                     |                                                       |
|---------------------------------------------------------------------|-------------------------------------------------------|
| 2.80                                                                | Length of Hypotenuse (mm):                            |
| 2.00                                                                | Length of Legs (mm):                                  |
| Optical Properties                                                  |                                                       |
| Aluminum with protective overcoat                                   | Coating:                                              |
| N-BK7                                                               | Substrate: <input type="checkbox"/>                   |
| 20-10                                                               | Surface Quality:                                      |
| ±2                                                                  | Angle Tolerance (arcmin):                             |
| Left-Handed                                                         | Image Orientation:                                    |
| Reflective Surfaces: R <sub>avg</sub> >85% FROM400-700nm, @ 45° AOI | Coating Specification:                                |
| 90                                                                  | Ray Deviation (°):                                    |
| 400 - 700                                                           | Wavelength Range (nm):                                |
| Hypotenuse: 0.3 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns            | Damage Threshold, By Design: <input type="checkbox"/> |
| 1.25                                                                | Power (fringes) @ 632.8nm:                            |
| 0.50                                                                | Irregularity (fringes) @ 632.8nm:                     |
| Regulatory Compliance                                               |                                                       |
| Compliant                                                           | RoHS 2015:                                            |
| Compliant                                                           | Reach 219:                                            |
| View                                                                | Certificate of Conformance:                           |



## Product Details

- Ray Deviation of 90°
- Left Handed Image
- Available with Aluminized and AR Coated Faces
- Additional [Right Angle Prism](#) Options Available


TECHSPEC® N-BK7 Right Angle Prisms are made from precision N-BK7 for use in a variety of visible light applications. Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image, and depending on the orientation of the prism, the image may be inverted or reverted. TECHSPEC® N-BK7 Right Angle Prisms can also be used in combination for image/beam displacement. These right-angle prisms are additionally offered with aluminized and AR Coated surfaces.

## Technical Information







Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).