

[See all 28 Products in Family](#)

TECHSPEC® 355nm, 12.5mm Diameter, Raman Edge Filter



Stock **#86-218** **3 In Stock**

⊖ 1 ⊕ **S\$779⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | S\$779.80 each |
| Qty 10-25 | S\$662.20 each |
| Qty 26-49 | S\$623.84 each |
| Need More? | Request Quote |

Product Downloads

General

Longpass Filter **Type:**

Bandwidth (nm): >400 **Note:**

Physical & Mechanical Properties

12.50 +0.0/-0.1 **Diameter (mm):**

>80 Clear Aperture (%):

Optical Properties

0 ±2 Angle of Incidence (°):

≥6.0 Optical Density OD (Average):

358.60 Cut-On Wavelength (nm):

355 Design Wavelength DWL (nm):

Fused Silica (Corning 7980) Substrate:

Hard Coated Coating:

60–40 Surface Quality:

>90 Transmission (%):

<3.6 Transition Width (nm):

<λ/4 @ 633nm Transmitted Wavefront, RMS:

Coating Specification:
T_{abs} ≥93% @ 364 - 400nm
T_{avg} ≥90% @ 364 - 800nm

355 - 800 Wavelength Range (nm):

355.00 Laser Blocking Wavelength (nm):

Threading & Mounting

3.5 Mount Thickness (mm):

Environmental & Durability Factors

Environmental: ML-STD-810F
Physical: ML-C-48497A Durability:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Transmission for Detecting Weak Signals
- Deep Blocking for Maximum Laser Rejection
- Ideal for Raman Spectroscopy or Life Science Instrumentation

TECHSPEC® Raman Longpass Edge Filters are single filter solutions for reducing spectral noise in Stokes shift applications. These filters are designed to create sharp transitions between transmitted Raman signals and blocked laser wavelengths. Designed to detect even the smallest Raman shifts, TECHSPEC Raman Longpass Edge Filters are ideal for integration into Raman spectroscopy or confocal microscopy systems. The hard coated design offers superior transmission characteristics than comparable traditional coated filters.

Compatible Mounts

