

[See all 102 Products in Family](#)

## 35mm Diameter x 26.2mm FL, MgF<sub>2</sub> Coated, Aspheric Condenser Lens



Stock **#15-537** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **S\$107<sup>10</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$107.10</b> each
Qty 11-49	<b>S\$96.60</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

35.00 +0.0/-0.4 **Diameter (mm):**

≤25 **Centering (arcmin):**

**Clear Aperture CA (mm):**

29.1

Edge Thickness ET (mm):

4.0

Center Thickness CT (mm):

13.90 ±0.25

Bevel:

Protective as needed

Diameter of Asphere (mm):

31.1

Shape of Back Surface:

Plano

### Optical Properties

Effective Focal Length EFL (mm):

26.20

Numerical Aperture NA:

0.61

Back Focal Length BFL (mm):

16.30

Substrate: □

[B270](#)

Focal Length Tolerance (%):

±7

Coating:

MgF<sub>2</sub> (400-700nm)

Coating Specification:

R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm

Surface Quality:

80-50 (typical)

f/#:

0.8

Abbe Number (v<sub>d</sub>):

58.5

Index of Refraction (n<sub>d</sub>):

1.523

Radius R<sub>2</sub> (mm):

Plano

Wavelength Range (nm):

400 - 700

Conjugate Distance:

Infinite

### Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

9.4

### Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:


[Compliant](#)

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information





## Coating Curves

---