

[See all 130 Products in Family](#)

TECHSPEC® 38.1mm Dia. 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #38-907 [CONTACT US](#)

1 **\$302⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$302.40 each
Qty 6-25	\$267.40 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

Clear Aperture (%):

Ground **Back Surface:**

38.10 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

Optical Properties

10-5 **Surface Quality:**

99.8 **Reflection at DWL (%):**

$R_{\text{abs}} \geq 99.8\%$ @ 1064nm **Coating Specification:**

1046 - 1074 **Wavelength Range (nm):**

$\lambda/10$ **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (1064nm) **Coating:**

1064 **Design Wavelength DWL (nm):**

0-45 **Angle of Incidence (°):**

[Fused Silica](#) (Corning 7980) **Substrate:**

15 J/cm² @ 1064nm, 20ns, 20Hz **Damage Threshold, Reference:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 209:**

[View](#) **Certificate of Conformance:**

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts