

[See all 5 Products in Family](#)

40mm Sq x 125mm FL 30° Off-Axis Parabolic Mirror



High Performance Off-Axis Parabolic Mirrors

Stock **#90-976** [CONTACT US](#)

⊖ 1 ⊕ **SS\$1,939⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-9	SS\$1,939.00 each
Qty 10-25	SS\$1,745.80 each
Qty 26-49	SS\$1,652.00 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

40.0 x 40.0 **Dimensions (mm):**

16.00 **Center Thickness CT (mm):**

±0.2	Center Thickness Tolerance (mm):
90.00	Clear Aperture (%):
+0.0/-0.2	Dimensional Tolerance (mm):
40.00	Length (mm):
40.00	Width (mm):
Optical Properties	
±2.0	Y Offset Tolerance (mm):
Metal	Coating Type:
Bare Aluminum	Coating:
30	Off-Set Angle (°):
134.00	Effective Focal Length EFL (mm):
Float Glass	Substrate: <input type="checkbox"/>
R _{abs} >85% @ 250 - 700nm	Coating Specification:
125.0	Parent Focal Length PFL (mm):
±0.5%	Parent Focal Length Tolerance (mm):
λ/2	Surface Accuracy:
80-50	Surface Quality:
268.00	Radius of Curvature (mm):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Quality Glass Substrate
- λ/4 or λ/2 Surface Accuracy
- Ideal for UV and Visible Applications


Our High Performance Off-Axis Parabolic Mirrors feature a superior surface accuracy glass substrate, making them ideal for UV and visible applications. Unlike standard parabolic mirrors, these off-axis mirrors direct and focus incident collimated light at a specific angle, allowing unrestricted access to the focal point. Typical applications include use in Czerny-Turner and Littrow spectrometer configurations, and in general collimator and beam expander setups.

High Performance Off-Axis Parabolic Mirrors have been replicated from masters which have passed stringent inspection criteria, including zonal interferometric and Foucault testing. The aspheric optical profile is holographically recorded onto the mirror substrate.

Note: The bare aluminum coating on these optics is delicate and can be easily scratched. If cleaning is required, non-contact methods such as compressed air or an air-blower should be used.

Technical Information

Parent Focal Length PFL	Reflected Effective Focal Length EFL	Y Offset	V	Off-Set Angle	Stock No.
125mm	134mm	67mm	9mm	30°	#90-976
200mm	209mm	85mm		24°	#90-977
275mm	279.1mm	67.5mm	4.1mm	14°	#90-978
					#90-980
	277.6mm	53mm	2.6mm	11°	#90-979



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools