

[See all 14 Products in Family](#)

50 x 300mm, Gimbal Crossmember Plate, Metric

See More by [Zaber™](#)



300mm, Gimbal Crossmember Plate

Stock **#71-112** **1 In Stock**

⊖ 1 ⊕ **S\$306^{.60}**

ADD TO CART

Volume Pricing	
Qty 1+	S\$306.60 each
Need More?	Request Quote

Product Downloads

General

Mounting Plate **Type:**

Zaber Technologies Inc. **Manufacturer:**

Physical & Mechanical Properties

50.00 **Length (mm):**

9.50 **Thickness (mm):**

300.00	Width (mm):
0.66	Weight (kg):

Threading & Mounting

(9) M6 x 1.0 tapped (8) M4 x 0.7	Mounting Threads:
-------------------------------------	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
---------------------------	-------------------

Product Details

- 360° Continuous Travel
- Speed up to 24°/s, Max Torque of 10N-m
- Max Centered Payload of 15kg; Max Cantilevered Load Capacity of 20N-m
- 300 and 500mm Payload Width Frame Options Available

Zaber™ High Load Capacity Motorized Gimbals are large, motorized two-axis rotation platforms that simplify the angular positioning of large components or subsystems within an optical system. All gimbals feature 360° continuous travel, two axis rotation around a single point, speed up to 24°/s, a Cantilevered Load Capacity of 20N-m, a rotary quadrature encoder resolution of 200 counts per revolution (CPR), and are available for payload widths of either 300 or 500mm. Drilled and tapped crossmember plates, used to create a mounting platform within the gimbal, are available with either English ([#71-113](#) or [#71-115](#)) or Metric ([#71-112](#) or [#71-114](#)) mounting options, and can also be used to quickly swap different components or pre-built subsystems into the gimbal. Zaber™ High Load Capacity Motorized Gimbals feature built-in controllers and motors allowing for closed-loop operation, slip/stall recovery, and independent axis control via a single RS-232 or USB connection for plug-and-play functionality and easy system integration. These gimbals are ideal for telecom, scanning, and tracking applications where high-load capacity and high-precision angular positioning is required.

Note: A [48 VDC universal power supply](#), [data cables](#) for daisy chaining, and computer interface cables ([USB](#) or [RS-232](#)) are sold separately as accessories. All Zaber™ High Load Capacity Motorized Gimbals are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#).