

[See all 31 Products in Family](#)

**TECHSPEC® 5mm Dia. x 15mm FL 785nm V-Coat, UV PCX Lens**



Stock #25-896 **5 In Stock**

⊖ 1 ⊕ **S\$198<sup>.00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | <b>S\$198.80</b> each         |
| Qty 6-25       | <b>S\$159.60</b> each         |
| Qty 26-49      | <b>S\$149.80</b> each         |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

5.00 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

Center Thickness CT (mm):

1.70

Centering (arcmin):

<1

Clear Aperture CA (mm):

4.5

Edge Thickness ET (mm):

1.23

## Optical Properties

Effective Focal Length EFL (mm):

15.00 @ 587.6nm

Substrate:

[Fused Silica](#)

f#:

3

Numerical Aperture NA:

0.17

Coating:

785nm V-Coat

Back Focal Length BFL (mm):

13.83

Coating Specification:

R<sub>abs</sub> <0.25% @ 785nm

Design Wavelength DWL (nm):

785

Focal Length Tolerance (%):

±1

Radius R<sub>1</sub> (mm):

6.88

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

1.5λ

Irregularity (P-V) @ 632.8nm:

λ/4

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

## Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.