

5X, Coherent® CO₂ Beam Expander

See More by [Coherent®](#)



CO₂ Beam Expanders

Stock **#11-365** **5 In Stock**

-

1

+

\$S\$1,117¹⁴

~~\$S\$1,396.42~~

ADD TO CART

Volume Pricing	
Qty 1-4	\$S\$1,396.42 \$S\$1,117.14 each
Qty 5-9	\$S\$1,254.54 \$S\$1,003.63 each
Qty 10-24	\$S\$1,112.66 \$S\$890.13 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Beam Expander

Type:

Fixed Magnification	Style:
Physical & Mechanical Properties	
57.58	Length (mm):
59	Weight (g):
30.48	Housing Diameter (mm):
Optical Properties	
0	Angle of Incidence (°):
High-Efficiency Anti-Reflective Coating (10.6μm)	Coating:
10600	Design Wavelength DWL (nm):
11.43	Entrance Aperture (mm):
22.86	Exit Aperture (mm):
5X	Expansion Power:
Zinc Selenide (ZnSe)	Substrate:
>99.4	Transmission (%):
R _{abs} <0.2% @ 10.6μm	Coating Specification:
10400 - 10600	Wavelength Range (nm):
Rotating Optics	Divergence Adjustment:
Threading & Mounting	
Input: Male M25 x 1	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Designed for CO₂ Laser Sources at 10.6μm
- Compact Housing for Easy System Integration
- Coherent® Infrared ZnSe Optical Elements

Coherent® CO₂ Beam Expanders are designed to collimate and improve the energy distribution of high power CO₂ laser beams. Featuring premier grade Zinc Selenide (ZnSe) optical elements from Coherent®, these beam expanders provide minimum beam deviation and greater than 99.4% transmission at 10.6μm. A high-efficiency anti-reflective coating on the ZnSe substrates results in reflectance less than 0.2% per surface and absorbance less than 0.1% per surface at 10.6μm. Coherent® CO₂ Beam Expanders feature a compact housing design with M25 input threading for easy integration into CO₂ laser systems. For additional expansion power options, please [contact us](#).

Note: IL-VI Incorporated is now Coherent Corp.

SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools