

[See all 21 Products in Family](#)

## 6 - 10mm FL, C-Mount, Manual Iris, Varifocal 4K Lens



Image represents #22-825; Design will vary by stock number.

Stock **#22-825** 1 In Stock

-

1

+

S\$1,764<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | S\$1,764.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

| Product Downloads |
|-------------------|
|-------------------|

| General                          |              |
|----------------------------------|--------------|
| Varifocal Lens                   | Type:        |
| Physical & Mechanical Properties |              |
| Manual Iris                      | Iris Option: |
| 46.50                            | Length (mm): |

|                       |                                               |
|-----------------------|-----------------------------------------------|
| 59                    | Maximum Diameter (mm):                        |
| 70                    | Weight (g):                                   |
| Optical Properties    |                                               |
| 112 - 44              | Horizontal Field of View @ Max Sensor Format: |
| 6-10                  | Focal Length Range (mm):                      |
| 500 - ∞               | Working Distance (mm):                        |
| F/1.7 to closed       | Aperture (f/#):                               |
| VIS                   | Lens Wavelength Range:                        |
| Sensor                |                                               |
| 1/1.7"                | Maximum Sensor Format:                        |
| Threading & Mounting  |                                               |
| C-Mount               | Mount:                                        |
| Regulatory Compliance |                                               |
| <a href="#">View</a>  | Certificate of Conformance:                   |

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.