

[See all 67 Products in Family](#)

# LightPath 354260 | 633nm Alignment, 0.16 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #67-724 **5 In Stock**

⊖ 1 ⊕ **S\$324<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$324.80</b> each
Qty 11-25	<b>S\$287.00</b> each
Qty 26-49	<b>S\$270.20</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

354260 **Lightpath Lens Code:**  
Fiber Collimator **Type:**

Lens Included:

#37-099

## Physical & Mechanical Properties

5.00 Clear Aperture CA (mm):

Protective as needed

Bevel:

Construction:

304L Stainless Steel Housing

11.00 Housing Diameter (mm):

20.2 Housing Length (mm):

## Optical Properties

15.29 @ 780nm Effective Focal Length EFL (mm):

0.16 Numerical Aperture NA:

Substrate:

D-ZK3

Coating:

BBAR (600-1050nm)

Coating Specification:

R<sub>abs</sub> <1.0% @ 600 - 1050nm

Surface Quality:

40-20

f#:

3.13

Wavelength Range (nm):

600 - 1050

Conjugate Distance:

Infinite

Alignment Wavelength (nm):

633

Transmitted Wavefront Error (λ, RMS):

< 0.090

## Hardware & Interface Connectivity

Connector:

SMA

## Threading & Mounting

Mount:

M11 x 0.5

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

## Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

## Technical Information

