


[See all 5 Products in Family](#)

# Everix Ultra-Thin OD 2 Longpass Filter, 700nm, 12.5mm Square

See More by [Everix](#)



Stock #35-127 CLEARANCE **6 In Stock**

⊖ 1 ⊕ **S\$103<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$103.60</b> each
Qty 11+	<b>S\$93.24</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Flexible Filter **Type:**

### Physical & Mechanical Properties

12.5 x 12.5 **Dimensions (mm):**

**Length (mm):**

12.50

Width (mm):

12.50

Dimensional Tolerance (mm):

±0.1

Clear Aperture (%):

>90

### Optical Properties

Optical Density OD (Average):

2.0 (absolute)

Cut-On Wavelength (nm):

700.00

Transmission (%):

>85 (average)

Cut-On Tolerance (%):

±3 typical

### Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

## Product Details

- Ultra-Thin, Flexible Substrate
- Sharp Cut-On Wavelength Designs
- Extruded Thin Film, Insensitive to Scratches

Everix Ultra-Thin Longpass Filters combine high performance and low cost in a new class of thin film interference filters that are flexible, scratch insensitive, and ultra-thin (200 - 500µm). These filters feature cut-on wavelengths in the visible range with cut-on tolerances of ±3% typical and >85% average transmission. The flexible extruded thin film filters are complex multilayer filters, which excel across a variety of needs, including longpass, edge, and notch filters. Everix Ultra-Thin Longpass Filters are ideal for demanding vision and medical technology applications.

**Note:** Custom filter designs can be purchased directly from [Everix](#).

## Technical Information

