

86mm x 46mm x 14mm Motorized Lens Controller



Motorized Telephoto Varifocal Lenses

Stock **#22-832** **1 In Stock**

-

1

+

S\$1,424⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,424.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Lens Accessory

Type:

Physical & Mechanical Properties

Weight (g):

86mm x 46mm x 14mm	Dimensions (mm):
Hardware & Interface Connectivity	
5V (via USB or pin)	Operating Voltage (V):
Threading & Mounting	
2x M4 with plastic housing	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- 9-36mm Focal Length Range with Fields of View Between 10 and 39°
 - NIR Corrected for Multi-Spectral and Day/Night Applications
 - Manual, P-Iris and DC Auto-Iris Models Available
- Motorized Telephoto Varifocal Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing the user to zoom in on an area of interest or zoom out for full scene investigation. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination. This IR correction will keep the image sharp in daylight, at night, or when there is a mix of visible and IR illumination. Motorized Telephoto Varifocal Lenses allow the user to optimize the field of view with 4X optical zoom capability to target an area of interest, then digitally zoom in up to 16X and are ideal for applications including Intelligent Traffic (ITS), remote sensing, security, and robotics.
- Note:** P-iris and DC auto-iris lenses are not compatible with standard machine vision cameras as they require a compatible auto-iris connector.