

[See all 102 Products in Family](#)

## 8mm Dia. x 5.6mm FL, Aspheric Condenser Lens



Stock **#19-510** **7 In Stock**

[Other Coating Options](#)

1  **\$55<sup>.65</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | <b>\$55.65</b> each           |
| Qty 11-49      | <b>\$50.40</b> each           |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Condenser Lens **Type:**

### Physical & Mechanical Properties

8.00 +0.0/-0.2 **Diameter (mm):**

≤30 **Centering (arcmin):**

**Clear Aperture CA (mm):**

7.2

Edge Thickness ET (mm):

1.33

Center Thickness CT (mm):

4.00 ±0.30

Bevel:

Protective as needed

Diameter of Asphere (mm):

8

Shape of Back Surface:

Convex

### Optical Properties

Effective Focal Length EFL (mm):

5.60

Numerical Aperture NA:

0.71

Back Focal Length BFL (mm):

3.3

Substrate:

H-ZK2

Focal Length Tolerance (%):

±5

Coating:

Uncoated

Surface Quality:

80-50 (typical)

f#:

0.7

Radius R<sub>2</sub> (mm):

16.52

Wavelength Range (nm):

350 - 2000

Conjugate Distance:

Infinite

### Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

## Technical Information



