

[See all 52 Products in Family](#)

**TECHSPEC® 8mm, f/1.8 Sealed UCw Series Fixed Focal Length Lens**



UCw Series Fixed Focal Length Lenses

Stock #70-595 **9 In Stock**

⊖ 1 ⊕ **\$394<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$394.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

UCw Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens with Compact Form Factor **Imaging Lens Type:**

**Physical & Mechanical Properties**

Fixed **Iris Option:**

42.00	<b>Length (mm):</b>
34	<b>Maximum Diameter (mm):</b>
30	<b>Outer Diameter (mm):</b>
5.15	<b>Maximum Rear Protrusion (mm):</b>
40.61	<b>Maximum Length (mm):</b>

## Optical Properties

44.7°	<b>Horizontal Field of View @ Max Sensor Format:</b>
44.7°	<b>Horizontal Field of View, 1/2" Sensor:</b>
40.7°	<b>Horizontal Field of View, 1/2.5" Sensor:</b>
33.9°	<b>Horizontal Field of View, 1/3" Sensor:</b>
25.6°	<b>Horizontal Field of View, 1/4" Sensor:</b>
8.00	<b>Maximum Image Circle (mm):</b>
0.03	<b>Numerical Aperture NA, Object Side:</b>
9 (8)	<b>Number of Elements (Groups):</b>
8.00	<b>Focal Length FL (mm):</b>
50 - ∞	<b>Working Distance (mm):</b>
f/1.8	<b>Aperture (f/#):</b>
M4 MgF <sub>2</sub>	<b>Coating:</b>
M4 MgF <sub>2</sub>	<b>Coating Specification:</b>
22.07	<b>Entrance Pupil Position (mm):</b>
27.98	<b>Object Space Principal Plane (mm):</b>
1.77	<b>Image Space Principal Plane (mm):</b>
-3.92	<b>Maximum Distortion (%):</b>
-20.88	<b>Exit Pupil Position (mm):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/2.5"	<b>Optimized Sensor Format:</b>
1/2"	<b>Maximum Sensor Format:</b>
1.85	<b>Pixel Size (µm):</b>

## Threading & Mounting

M43 x0.75 (Male)	<b>Filter Thread:</b>
<a href="#">#89-940 (Required)</a>	<b>Filter Thread Adapter:</b>
M34.0 x0.5 (Male)	<b>Front Thread:</b>
C-Mount	<b>Mount:</b>

## Environmental & Durability Factors

IPX7	<b>Environmental Rating:</b>
-20 to +60 For questions regarding operating temperature please contact our support team	<b>Storage Temperature (°C):</b>

---

Waterproof (IPX7) **Type of Ruggedization:**

---

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

## Product Details

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.

---