

940nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock #65-670 3-5 DAYS

⊖ 1 ⊕ **S\$129.05**

ADD TO CART

Qty 1-9

S\$129.05

Qty 10+

S\$116.43

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):
9.0

Center Wavelength CWL (nm):
940.00 ±2

Center Wavelength CWL Tolerance (nm):
±2

Full Width-Half Max FWHM (nm):
10.00 ±2

Full Width-Half Max FWHM Tolerance (nm):
±2

Minimum Transmission (%):
≥50

Operating Temperature (°C):
-50 to +75

Coating:
Traditional Coated

Surface Quality:
80-50

Thickness Tolerance (mm):
±0.1

Type:
Bandpass Filter

Typical Applications:
InGaAs

Blocking Wavelength Range (nm):
200 - 1200

Construction:
Mounted in Black Anodized Ring

Mount Thickness (mm):
7.5 ±0.1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)