

Coherent® PowerMax USB PS19 Measurement System 1174261 | 1W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-412** **4 In Stock**

-

1

+

S\$3,255^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$3,255.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

PS19
Coherent Part Number: 1174261

Model Number:

Meterless

Type:

±1

Linearity (%):

±2	Calibration Uncertainty (%):
----	------------------------------

0.001 - 1	Long Pulse Joule Mode Range (J):
±3	Long Pulse Joule Mode Accuracy (%):

Air	Cooling Method:
2	Response Time (s):

50mJ/cm ² (10ns, 1064nm)	Maximum Incident Energy Density:
-------------------------------------	----------------------------------

Physical & Mechanical Properties

19	Active Area Diameter (mm):
----	----------------------------

Optical Properties

514	Calibration Wavelength (nm):
300 - 11000	Wavelength Range (nm):
0.3 - 11	Wavelength Range (μm):

Sensor

Thermopile	Type of Sensor:
------------	-----------------

Electrical

±1.5	Spectral Compensation Accuracy (%):
0.5	Maximum Incident Power Density (kW/cm ²):
100μW - 1W	Power Range:
1	Maximum Power (W):
5μW	Noise Equivalent Power:

Hardware & Interface Connectivity

2.5	Length of Cable (m):
USB	Computer Interface:

Environmental & Durability Factors

Yes	Thermally Stabilized:
-----	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².