

[See all 7 Products in Family](#)

Coherent® High-Sensitivity Thermopile Sensor PM3 1098336 | 2W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-403** **6 In Stock**

S\$1,638⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,638.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
PM3 Coherent Part Number: 1098336

Type:
[Meter required](#)

Linearity (%):
±1

Calibration Uncertainty (%):
1

Cooling Method:

Air

Response Time (s):

2

Note:

Includes a Removable 10mm ID Light Tube to Eliminate Stray Light

Compatible Meters:

[#35-203](#), [#12-393](#), [#59-978](#),
[#88-411](#), [#66-277](#), [#88-412](#)

Maximum Incident Energy Density:

50mJ/cm² (10ns, 1064nm)

Physical & Mechanical Properties

Active Area Diameter (mm):

19

Optical Properties

Calibration Wavelength (nm):

514

Wavelength Range (nm):

300 - 11000

Wavelength Range (µm):

0.3 - 11

Sensor

Type of Sensor:

Thermopile

Electrical

Maximum Incident Power Density (kW/cm²):

0.5

Power Range:

500µW - 2W

Maximum Power (W):

2

Power Resolution:

50µW

Hardware & Interface Connectivity

Length of Cable (m):

2

Computer Interface:

DB-25

Environmental & Durability Factors

Thermally Stabilized:

No

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Product Details

- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².