

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NOA 65 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#55-087** **20+ In Stock**

⊖ 1 ⊕ **\$47<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-11	<b>\$47.60</b> each
Qty 12-19	<b>\$42.84</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

0.34 **Size (oz):**

65 **Norland Number:**

6 months **Shelf Life:**

Barrel **Type:**

**Typical Applications:**

More flexible adhesive for extra low strain applications. Suitable for cold blocking applications.

**Note:**

Contains 10g of adhesive

**Physical & Mechanical Properties**

10.00 **Size (cc):**

**Optical Properties**

1.52 @ 589nm **Index of Refraction (n<sub>d</sub>):**

350 - 380 **Absorption Range (nm):**

**Material Properties**

Good **Glass Bonding:**

Good **Metal Bonding:**

Fair **Plastic Bonding:**

1200 **Viscosity (cps):**

Glass to Glass/Metal **Bonding Type:**

4.5 **Energy for Full Cure (J/cm<sup>2</sup>):**

**Environmental & Durability Factors**

Flexible **Durability:**

**Regulatory Compliance**

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 253:**

**Product Details**

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

**Technical Information**

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

