

[See all 4 Products in Family](#)

## Fiber Coupling Adapter



Fiber Coupling Adapter

Stock **#26-741** **2 In Stock**

⊖ 1 ⊕ **\$\$712<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>\$\$712.60</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Hardware & Interface Connectivity

SMA **Connector:**

### Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Two Color Si-InGaAs Chip for 320 – 1700nm Wavelength Range
- Embedded 24-Bit Analog-to-Digital Converter
- Digital USB Connection and Two Analog BNC Connections

NIREOS SPIDER High-Dynamic Range VIS-SWIR Photodetector is a broadband, amplified Si-InGaAs photodetector that allows for analog or digital connection and enables rapid development of high-performance sensing and spectroscopy solutions suitable in industrial, laboratory, and research environments. Featuring a two-color Si and InGaAs chip, this photodetector allows straightforward beam alignment and achieves a wide spectral response ranging from 320 - 1700nm. With an embedded 24-bit analog-to-digital converter (ADC), the Si and InGaAs analog outputs are simultaneously digitized with adjustable sampling rates from 0.5 to 120kSPS via USB connection. NIREOS SPIDER High-Dynamic Range VIS-SWIR Photodetector's Si and InGaAs channels are both independently amplified with analog bandwidths up to 56kHz, picowatt sensitivity, and 8 switchable transimpedance gain options ranging from 1.5k $\Omega$  to 4.4M $\Omega$ . This photodetector comes with a user friendly, plug-and-play software for ease of setup, and features DLLs allowing for programming using .NET based languages such as C++, C#, LabView, Python, and MATLAB.

## Technical Information

