

[See all 9 Products in Family](#)

## High Contrast NIR Polarizing Film, 76mm x 76mm



High Contrast NIR Polarizing Film

Stock **#25-104** **5 In Stock**

⊖ 1 ⊕ S\$686<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	S\$686.00 each
Qty 10+	S\$550.48 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Linear Polarizer **Type:**

**Note:**  
Delivered with protective film and paper overlayer on both sides marked to show polarization axis. Outer 0.5mm edge is not functional due to loss of transparency during laser cutting.

### Physical & Mechanical Properties

**Length (mm):**

76.00

**Dimensions (mm):**

76.0 x 76.0 ±0.2

**Thickness (mm):**

0.50 (Nominal)

**Construction:**

Polarizing Film

**Width (mm):**

76.00

### Optical Properties

**Coating:**

Uncoated

**Extinction Ratio:**

>1000:1 (700nm-1600nm)  
>10000:1 AVG (400nm-800nm)

**Substrate:**

Cellulose Triacetate

**P-Polarization Transmission (%):**

532nm: 65  
830nm: 70  
1550nm: 80

**S-Polarization Transmission (%):**

532nm: 0.002  
830nm: 0.04  
1550nm: 0.1

**Surface Quality:**

80-50

**Wavelength Range (nm):**

420 - 1600

### Environmental & Durability Factors

**Heat Resistance (°C x Hours):**

85 x 500 (dry)

**Cold Resistance (°C x Hours):**

-40 x 500

**Environmental Durability:**

DIN ISO 9022-2-10-07  
DIN ISO 9022-2-11-05  
DIN ISO 9022-2-12-07  
DIN ISO 9022-2-14-05

**Storage Temperature (°C):**

15-25

### Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 253:**

[Compliant](#)

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- >1,000:1 Extinction Ratio from 700nm-1600nm
- Ideal for NIR Imaging Applications
- Affordable Alternative to Conventional Glass Polarizers
- [Ultra-Broadband NIR Polarizing Films](#) also Available

High Contrast Near-Infrared (NIR) Polarizing Film provides excellent contrast in the VIS and NIR spectrum and is an affordable alternative to conventional glass polarizers. These polarizing films are designed for assisting stray light management with NIR photodetectors and glare reduction in industrial imaging applications. With 1,000:1 contrast in NIR and 10,000:1 contrast in VIS, these polarizing films have excellent broadband performance. High Contrast Near-Infrared (NIR) Polarizing Film features high transmission between 415 - 1600nm and can be easily cut to size. These polarizing films are ideal for the use in sensing, NIR imaging, and SWIR applications.