

[See all 65 Products in Family](#)

# IDS Imaging U3-3884LE-C-HQ-VU 1/1.8" Color USB3 Camera Rev. 1.2 (Recertified 05-P)

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #78-149-RCD-05P **RECERTIFIED** 1 In Stock

- 1 + S\$378<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	S\$378.60 each
Need More?	<a href="#">Request Quote</a>

#### Product Downloads

Color	Spectrum:
-------	-----------

#### General

Color Camera	Type:
--------------	-------

#### Sensor

1/1.8"	Sensor Format:
--------	----------------

6.40	<b>Resolution (Megapixels):</b>
54.00	<b>Frame Rate (fps):</b>
3,088 x 2,076	<b>Pixels (H x V):</b>
2.40 x 2.40	<b>Pixel Size, H x V (µm):</b>
Sony IMX178	<b>Imaging Sensor:</b>
Rolling	<b>Shutter Type:</b>

## Hardware & Interface Connectivity

Vertical	<b>Connector:</b>
----------	-------------------

## Threading & Mounting

C-Mount	<b>Mount:</b>
---------	---------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.