

# Infinimite Mounting Clamp

See More by [Infinity Photo-Optical Company](#)



Stock #54-591 CLEARANCE 1 In Stock

-

1

+

S\$77<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | S\$77.00 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|                |       |
|----------------|-------|
| Lens Accessory | Type: |
|----------------|-------|

Regulatory Compliance

|                           |            |
|---------------------------|------------|
| <a href="#">Compliant</a> | RoHS 2015: |
| <a href="#">Compliant</a> | Reach 224: |

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|


## Product Details

- 3 Primary Magnification Range Options
- Working Distance from 25mm to Infinity
- Optional [LDL](#) Doubler Tube Boosts Magnification 2X

The InfiniMte™ Imaging Lenses are available in 3 lens power ranges. The standard version uses an integral focus lock as a friction brake to lock the magnification/focus setting in place. Designed with input from specialists in the field, its miniature size allows the InfiniMte™ to be integrated into a wide variety of electronic imaging conditions. The length of the lens does not change when focusing. InfiniMte™ Imaging Lenses were designed to provide specific working distance and field of view combinations when using 1/3" format sensors, but the lenses can be used with sensors up to 2/3" format.

The main lens, the Alpha, covers a 0.75- 0.08X range for macro use, whereas the Beta and Gamma versions offer a working distance (WD) shift from the high-magnification end of the Alpha. For example, with a ½" sensor, the Alpha gives a ½" field of view (FOV) at 40mm WD at 0.5X Lens magnification (PM); at the same PM& FOV, the Beta has a 60mm WD and the Gamma has a 122mm WD. The three lens options offer unprecedented flexibility in system integration.

## Technical Information



| Working Distance                 | 25mm  | 40mm   | 60mm   | 80mm   | 170mm  | 230mm  | 295mm  |
|----------------------------------|-------|--------|--------|--------|--------|--------|--------|
| Primary Magnification            | 0.75X | 0.50X  | 0.33X  | 0.25X  | 0.13X  | 0.10X  | 0.08X  |
| Field of View, ½" Sensor Horiz   | 8.5mm | 12.8mm | 19.4mm | 25.6mm | 51.2mm | 64.0mm | 80.0mm |
| Field of View, 1/3" Sensor Horiz | 6.4mm | 9.6mm  | 14.5mm | 19.2mm | 38.4mm | 48.0mm | 60.0mm |

| Working Distance                 | 55mm  | 60mm   | 90mm   | 120mm  | 240mm  | 317mm  | 400mm  |
|----------------------------------|-------|--------|--------|--------|--------|--------|--------|
| Primary Magnification            | 0.66X | 0.50X  | 0.33X  | 0.25X  | 0.13X  | 0.10X  | 0.08X  |
| Field of View, ½" Sensor Horiz   | 9.7mm | 12.8mm | 19.4mm | 25.6mm | 49.2mm | 64.0mm | 80.0mm |
| Field of View, 1/3" Sensor Horiz | 7.3mm | 9.6mm  | 14.5mm | 19.2mm | 36.9mm | 48.0mm | 60.0mm |

| Working Distance                 | 122mm  | 165mm  | 213mm  | 396mm  | 515mm  | 640mm  |
|----------------------------------|--------|--------|--------|--------|--------|--------|
| Primary Magnification            | 0.50X  | 0.33X  | 0.25X  | 0.13X  | 0.10X  | 0.08X  |
| Field of View, ½" Sensor Horiz   | 12.8mm | 19.4mm | 25.6mm | 51.2mm | 64.0mm | 80.0mm |
| Field of View, 1/3" Sensor Horiz | 9.6mm  | 14.5mm | 19.2mm | 38.4mm | 48.0mm | 60.0mm |