

[See all 14 Products in Family](#)

LightPath 390036 | 6.5mm Dia., 0.56 NA, BBAR (3000-5000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock **#66-561 8 In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$574⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$574.00 each
Qty 11-49	S\$516.60 each
Need More?	Request Quote

Product Downloads

General	
390036	Lightpath Lens Code:
Aspheric Lens	Type:

Physical & Mechanical Properties

6.50 ±0.015	Diameter (mm):
-------------	----------------

5.00	Clear Aperture CA (mm):
1.94	Edge Thickness ET (mm):
2.50	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

4.00 @ 2500nm	Effective Focal Length EFL (mm):
---------------	----------------------------------

0.56	Numerical Aperture NA:
------	------------------------

Black Diamond™ BD-2 (Ge ₂₆ Sb ₁₂ Se ₆₀)	Substrate: ☐
---	-------------------------------------

2500	Aspheric Design Wavelength (nm):
------	----------------------------------

BBAR (3000-5000nm)	Coating:
--------------------	----------

R _{avg} <1.0% @ 3 - 5µm	Coating Specification:
----------------------------------	------------------------

80-50	Surface Quality:
-------	------------------

0.89	f/#:
------	------

2.6023	Index of Refraction (n _d) @ 10µm:
--------	---

2.5843	Index of Refraction (n _d) @ 14µm:
--------	---

2.6210	Index of Refraction (n _d) @ 4µm:
--------	--

2.6173	Index of Refraction (n _d) @ 5µm:
--------	--

3000 - 5000	Wavelength Range (nm):
-------------	------------------------

3.05	Working Distance (mm):
------	------------------------

Infinite	Conjugate Distance:
----------	---------------------

Material Properties

4.68	Density (g/cm ³):
------	-------------------------------

70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 µm)	Thermo-optic coefficient dn/dT:
--	---------------------------------

285.00	Transformation Temperature (°C):
--------	----------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
-----------	------------

View	Certificate of Conformance:
------	-----------------------------


Compliant	Reach 247:
-----------	------------

Product Details

- Wavelength Range of 1.8 - 12µm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12µm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information



Compatible Mounts

;