

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110744 | Nd:YAG Sensor, 1.5mJ-3J, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock #66-278 **6 In Stock**

⊖ 1 ⊕ S\$2,905⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,905.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
J-50MB-YAG
Coherent Part Number: 1110744

Type:
[Meter required](#)

Linearity (%):
±3

Calibration Uncertainty (%):
±2

Noise Equivalent Energy (μJ):

<50

Compatible Meters:

[#35-203](#), [#66-277](#), [#88-412](#)

Maximum Incident Energy Density:

14J/cm² (10ns, 1064nm)
2.8J/cm² (10ns, 532nm)
0.75J/cm² (10ns, 355nm)
1.0J/cm² (10ns, 266nm)

Energy Range:

1.5mJ - 3J

Preferred Meter:

[#66-277](#)

Physical & Mechanical Properties

Active Area Diameter (mm):

35

Optical Properties

Calibration Wavelength (nm):

1064

Maximum Pulse Width (μs):

340

Wavelength Range (nm):

266 - 2100

Sensor

Type of Sensor:

Pyroelectric

Electrical

Maximum Repetition Rate (pps):

50

Maximum Incident Beam Power (W):

20

Hardware & Interface Connectivity

Connector:

DB25

Length of Cable (m):

2.5

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.