

[See all 13 Products in Family](#)

M27 x 0.5 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-896** **7 In Stock**

S\$75⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$75.60 each
Qty 10-25	S\$68.25 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

23.00 **Clear Aperture CA (mm):**

29.00 **Diameter (mm):**

Construction:

Dichroic

Optical Properties

Uncoated
Coating:
Extinction Ratio:
Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Float Glass
Substrate: □
Polarization:
95% Efficiency

Single: 30
Crossed: 0.15
Transmission (%):
Wavelength Range (nm):
400 - 700

Threading & Mounting

M27 x 0.50
Filter Thread:
Mount Thickness (mm):
8
Mount Thickness Including Threads (mm):
10

Environmental & Durability Factors

Operating Temperature (°C):
-15 to +70

Regulatory Compliance

View
Certificate of Conformance:

Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

Technical Information

