

## M34.5 x 0.5 Thread, Ring Light Filter Thread Adapter



#56-090: M34.5 x 0.5 Thread, Ring Light Filter Thread Adapter

Stock **#56-090** CLEARANCE **8 In Stock**

S\$64<sup>33</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>S\$64.33</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Accessory **Type of Illumination:**

**Physical & Mechanical Properties**

Anodized Aluminum **Construction:**

**Threading & Mounting**

M34.5 x 0.50 **Filter Thread:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 235:**

## Product Details

- Compatible with LED Ring Lights
- Common Filter Thread Sizes Available
- Allows for Easy Integration of LED Ring Lights

Ring Light Filter Thread Adapters allow our LED ring lights to connect directly to an [imaging lens](#). The adapter slides into a flange protruding from the back of the ring light. Select the ring light adapter with the threading that matches the front filter threading of the lens. All feature an anodized aluminum construction.

**Note:** Though Ring Light Filter Thread Adapters can work with a wide range of imaging lenses, the working distance and field coverage provided by the LED ring light must be considered. Vignetting may occur on very wide angle imaging lenses.

## Technical Information

| Filter Thread | Imaging Lenses Available to Use with Adapters   | Adapter Stock No.       |
|---------------|---|-------------------------|
| M25.5 x 0.5   | 8.5/12/16/25/35/50/75mm <a href="#">C Series Fixed Focal Length Lenses</a>  | <a href="#">#56-523</a> |
| M30.5 x 0.5   | 18mm and 25mm <a href="#">DG Series FFL</a> , <a href="#">28mm Rodagon</a> , <a href="#">MegaPixel Fixed Focal Length</a> (vignetting may occur with large format sensors), <a href="#">Compact VIS-NIR Lenses</a> (vignetting may occur with large format sensors) | <a href="#">#56-089</a> |
| M34.5 x 0.5   | <a href="#">3.3X Macro Zoom Lens</a>  | <a href="#">#56-090</a> |
| M37 x 0.75    | <a href="#">MMS®</a> , 35mm <a href="#">DG Series FFL</a> , 0.50X and 1.0X <a href="#">SilverTL™ Telecentric</a>  | <a href="#">#56-091</a> |
| M39 x 0.5     | 50mm <a href="#">DG Series FFL</a>  | <a href="#">#56-092</a> |
| M40.5 x 0.5   | <a href="#">7X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 35/50/60/80/105/135mm <a href="#">Rodagon Lenses</a> , 0.60X <a href="#">SilverTL™ Telecentric Lenses</a>  | <a href="#">#56-093</a> |
| M43 x 0.75    | <a href="#">55mm Telecentric</a> , 0.30X/0.40X/2.0X <a href="#">SilverTL™ Telecentric</a>   | <a href="#">#56-094</a> |
| M46 x 0.75    | <a href="#">10X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 0.25X <a href="#">SilverTL™ Telecentric</a>   | <a href="#">#56-095</a> |
| M49 x 0.75    | 75mm <a href="#">DG Series FFL</a>  | <a href="#">#56-096</a> |
| M52 x 0.75    | <a href="#">6X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), <a href="#">TECHSPEC® LS Series Fixed Focal Length Lenses</a>  | <a href="#">#56-097</a> |
| M58 x 0.75    | 0.36X/0.5X <a href="#">GoldTL™ Telecentric</a> , 0.20X/4.0X <a href="#">SilverTL™ Telecentric</a>   | <a href="#">#56-098</a> |
| M62 x 0.75    | 0.73X/1X <a href="#">GoldTL™ Telecentric</a> , 0.16X <a href="#">SilverTL™ Telecentric</a>  | <a href="#">#56-099</a> |
| M72 x 0.75    | 0.18X/0.25X <a href="#">GoldTL™ Telecentric</a>   | <a href="#">#56-100</a> |

| Compatible Ring Lights  |
|---|
| <a href="#">Advanced Illumination Standard Working Distance LED Ring Lights</a> |
| <a href="#">Advanced Illumination Extended Working Distance LED Ring Lights</a> |
| <a href="#">Advanced Illumination Brightfield/Darkfield LED Ring Lights</a>     |
| <a href="#">Advanced Illumination 5" Darkfield LED Illuminators</a>             |