

[See all 26 Products in Family](#)

M4060, 1" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie[™] Nano 5GigE Cameras (Front)



Stock **#16-030** **1 In Stock**

[Similar Cameras](#)

-

1

+

S\$4,165⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$4,165.00 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

G5-GM30-M4060

Model Number:

Teledyne DALSA	Manufacturer:
Genie Nano-5GigE	Camera Series:
Physical & Mechanical Properties	
59 x44 x42.6 (includes connectors and lens mount)	Dimensions (mm):
124	Weight (g):
Full	Housing:
Sensor	
450MB	Image Buffer:
1"	Sensor Format:
8.90	Resolution (Megapixels):
68.00	Frame Rate (fps):
4,112 x2,176	Pixels (H x V):
3.45 x3.45	Pixel Size, H x V (µm):
14.19 x7.51	Sensing Area, H x V (mm):
Sony IMX255	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8 bit	Pixel Depth:
Automatic, Programmable, or via External Trigger	Exposure Time:
76.46	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:
Electrical	
9.4 - 9.6	Power Consumption (W):
Hardware & Interface Connectivity	
5GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO	Power Supply:
2 digital input, 3 digital output	GPIOs:
Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
10-pin Samtec	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #34-966	Mounting Threads:
Environmental & Durability Factors	
-20 to +65	Operating Temperature (°C):
-40 to +80	Storage Temperature (°C):

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- 5GBASE-T (5GigE) Ethernet Interface
- 3.2 to 12.4 Megapixel Sensors
- TurboDrive™ Technology for Data Transfer Speeds up to 985 MB/s
- Compact (32 x 44 x 59mm), Lightweight, and Robust Design



Teledyne DALSA Genie™ Nano 5GigE Cameras are available with a range of SONY Pregius sensors with resolutions from 3.2MP to 12.4MP. The 5GigE Ethernet interface provides data transfer speeds up to 5 times faster than the conventional GigE interface, which when combined with TurboDrive™ technology allows these cameras to achieve frame rates up to 187fps while retaining full image quality. The included Sopera CamExpert software provides a simple image acquisition interface with Sopera LT SDK libraries for OEM and system integration applications. Teledyne DALSA Genie™ Nano 5GigE Cameras are packaged in a compact, lightweight and robust all-metal housing, making them ideal for electronics inspection, industrial automation, and Intelligent Traffic Systems (ITS) applications. These cameras support the AIA GigE Vision Standard to facilitate easy integration into imaging systems.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sopera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sopera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sopera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.