

## M49 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-443 3-5 DAYS

⊖ 1 ⊕ **S\$110.92**

**ADD TO CART**

Qty 1-9

**S\$110.92**

Qty 10+

**S\$106.28**

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Clear Aperture CA (mm):**

44.00

**Coating:**

Hardcoated

**Diameter (mm):**

51.00

**Extinction Ratio:**

up to 3000:1 @~600nm (nominal)

**Filter Thread:**

M49 x 0.75

**Surface Quality:**

40-20

**Type:**

Mounted Imaging Filter

**Construction:**

Black Anodized Aluminum

**Wavelength Range (nm):**

400 - 700

**Mount Thickness Including Threads (mm):**

9.6

## Regulatory Compliance

**RoHS:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

---