

[See all 6 Products in Family](#)

# Optotune Industrial 1 Channel Current Controller | ICC-1C

See More by [Optotune](#)



Optotune Industrial 1 Channel Current Controller | ICC-1C - Front



Stock #74-605 **NEW** [CONTACT US](#)

- 1 + **S\$819<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>S\$819.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

SpecialtyLens **Type:**

**Physical & Mechanical Properties**

28.7 **Height (mm):**

64.00 **Length (mm):**

105.00	<b>Width (mm):</b>
<b>Electrical</b>	
-500 to +500	<b>Operating Current (mA):</b>
15 (maximum)	<b>Power Consumption (W):</b>
<b>Hardware &amp; Interface Connectivity</b>	
<b>Connector:</b> USB-C, Ethernet (to PC), 6-way Hirose (to lens)	
<b>Environmental &amp; Durability Factors</b>	
0 to +60	<b>Operating Temperature (°C):</b>
-40 to +85	<b>Storage Temperature (°C):</b>
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- ICC-1C for Control of a Single Optotune Lens
- ICC-4C-500 Controls Up to 4 Optotune Lenses Simultaneously
- ICC-4C-2000 Controls Optotune Beam Shifters and Fine Steering Mirrors
- Driven via Optotune Cockpit GUI, SDK, or Analog Signal
- [Optotune Lens Drivers](#) and [Gardasoft Controllers](#) Also Available

Optotune ICC Current Controllers allow for control of Optotune Focus Tunable Lenses delivering  $\pm 500\text{mA}$  of current (up to 4 lenses can be controlled with [ICC-4C-500](#)), or of Optotune's Beam Shifters and Fine Steering Mirrors ([ICC-4C-2000](#)). The controller features a variety of interfaces to facilitate easy communication with existing machine vision systems, including USB, UART, I2C, Ethernet, and analog input. The Optotune Cockpit GUI is used to easily drive the controller over USB or ethernet with Python and C# SDKs available for further user integration. Optotune ICC Current Controllers are ideal for machine vision applications and for using multiple liquid lenses to simplify control and wiring. These controllers also offer the ability to control LEDs, laser diodes, thermo-electric coolers (TECs), or other devices requiring accurate current control. The extension kit [#22-409](#) is required for driving Optotune Focus Tunable Lenses with FPC connectors using the [ICC-1C](#) or [ICC-4C-500](#), and the extension kit [#23-718](#) is required for driving Beam Shifters and Fine Steering Mirrors with the [ICC-4C-2000](#).

## Technical Information

OPTOTUNE ICC-4C-500 CONTROLLER PRODUCTS			
Stock Number	Description	Contents	Notes
<a href="#">#22-408</a>	ICC-4C-500 Controller	<ul style="list-style-type: none"> <li>• ICC-4C-500 Controller only</li> </ul>	Used to control up to 4 Optotune lenses with Hirose connectors simultaneously (up to $\pm 500\text{ mA}$ per channel). Power supply sold separately and required ( <a href="#">#22-410</a> ). To control Optotune lenses with FPC connectors, <a href="#">#22-409</a> is also required. For I/O input, users must supply their own I/O connector.
<a href="#">#22-409</a>	ICC-4C-500 Extension Kit	<ul style="list-style-type: none"> <li>• Adaptor board for lenses (with 30 cm extension cable)</li> <li>• Micro-USB cable</li> <li>• DIN Rail clamp Kit</li> </ul>	Used with the ICC-4C-500 Controller ( <a href="#">#22-408</a> ) to control up to 4 Optotune lenses with FPC connectors simultaneously. Plugs directly into the auxiliary output connector, or with included extension cable.
<a href="#">#22-410</a>	ICC-4C Power Adapter	<ul style="list-style-type: none"> <li>• Power adapter with US main cable</li> </ul>	Includes AC/DC adapter that interfaces with the ICC-4C and US main cable.

OPTOTUNE ICC-4C-2000 CONTROLLER PRODUCTS			
Stock Number	Description	Contents	Notes
<a href="#">#23-717</a>	ICC-4C-2000 Controller	<ul style="list-style-type: none"> <li>• ICC-4C-2000 Controller only</li> </ul>	Used to control Optotune's XPR Beam Shifters, <a href="#">BSW-20 Beam Shifters</a> , and <a href="#">FMR-20 Fine Steering Mirrors</a> . Provides 4 independent channels with $\pm 2\text{ A}$ per channel. Power supply and extension kit sold separately and required ( <a href="#">#23-718</a> and <a href="#">#22-410</a> ). For I/O input, users must supply their own I/O connector.
<a href="#">#23-718</a>	ICC-4C-2000 Extension Kit	<ul style="list-style-type: none"> <li>• Adapter board for XPRs, BSW and FMR (with 20 cm extension cable)</li> <li>• Micro-USB cable</li> <li>• DIN Rail clamp Kit</li> </ul>	Used with the Optotune ICC-4C-2000 controller to interface with XPR, BSW-20, and FMR-20 products through FPC interface. Plugs directly into the 34-pin output connector, or with included extension cable.
<a href="#">#22-410</a>	ICC-4C Power Adapter	<ul style="list-style-type: none"> <li>• Power adapter with US main cable</li> </ul>	Includes AC/DC adapter that interfaces with the ICC-4C and US main cable.

