

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NOA 1622H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-381** [CONTACT US](#)

- 1 + **\$80<sup>.50</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>\$80.50</b> each
Qty 5-11	<b>\$72.52</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

0.34	<b>Size (oz):</b>
1622H	<b>Norland Number:</b>
4 months	<b>Shelf Life:</b>
Barrel	<b>Type:</b>

Bonding glass to glass **Typical Applications:**

**Note:**  
Contains 10g of adhesive. This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.

### Optical Properties

1.622 **Index of Refraction (n<sub>d</sub>):**  
315 - 395 **Absorption Range (nm):**

### Material Properties

Excellent **Glass Bonding:**  
Excellent **Metal Bonding:**  
Excellent **Plastic Bonding:**  
220 **Viscosity (cps):**  
Glass to Glass **Bonding Type:**  
6 **Energy for Full Cure (J/cm<sup>2</sup>):**

### Environmental & Durability Factors

Soft & Flexible **Durability:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**  
[View](#) **Certificate of Conformance:**  
[Compliant](#) **Reach 253:**

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.