

[See all 31 Products in Family](#)

SCHOTT EasyLED Ring Light

See More by [SCHOTT Optical Components](#)



Stock #15-905 **3 In Stock**

⊖ 1 ⊕ \$966⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	\$966.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Operating Lifetime (hours):
>50,000

Model Number:
600.200

Intensity Control Option:
Yes

45

Number of LEDs:

LED Illuminator

Type of Illumination:

SCHOTT

Manufacturer:

Ring Light

Geometry:

Constant

Illumination Mode:

Physical & Mechanical Properties

66

Inner Diameter (mm):

114

Outer Diameter (mm):

Optical Properties

White

Color:

55 - 135

Working Distance (mm):

Hardware & Interface Connectivity

12 DC

Input Voltage (V):

Power Supply:
Power supply included. If additional power supplies are required, see [#15-907](#)

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Ringlight, Backlight, and Spotlight Illuminators
- Integrated Controllers for Intensity Adjustment
- Designed for Easy Integration into Microscopy Systems

SCHOTT EasyLED Series Illuminators are compact illuminators with integrated controllers that provide continuous intensity adjustment. These illuminators are available as ringlights, backlights, or spotlights, and accessories are available to integrate each type of illuminator into microscopy systems. EasyLED Ringlights offer homogenous, shadow-free illumination, while the Ringlights Plus also features controllable LED segments for enhanced contrast adjustment. EasyLED Backlights are designed to fit common microscope stand sizes from 84 to 180mm in diameter and provide uniform illumination over their large 50mm diameter active area. EasyLED Spotlights can be mounted to any microscope stand to facilitate integration into existing microscopy systems and are available with one or two adjustable spotlights. SCHOTT EasyLED Series Illuminators are an ideal replacement for conventional cold light sources using fiber optics in machine vision or microscopy applications.

Technical Information

System Diagram for EasyLED Series

